



GEM-2® Sensor Flushometer

GEM-2 180 SMO

Product description

GEM-2® Exposed Sensor Urinal Flushometer.

Compliances & Certifications



(ADA Compliant*, BAA Compliant, IAPMO, UPC Certified)

Listed compliances and certifications may vary based on product variation.

Finish



Available in Polished Chrome (CP).

Downloads

- [GEM_GEM 2 Piston Type Exposed Installation Instructions](#)
- [Optima SMO Installation Instructions](#)
- [EBV-157-A Handle Adapter Kit Installation Instructions](#)
- [Control Stop Repair and Maintenance Guide](#)
- [Flush Connections Flanges Repair and Maintenance Guide](#)
- [Flushometers Brochure](#)
- [Additional Downloads](#)

Videos

- [Sloan – Company Overview](#)

Features

- Fixed volume piston with filtered O-ring bypass and ADA-compliant, metal oscillating, non-hold-open handle ensure reliable, water-efficient operation
- Integrity of the product is maintained with control stop plug
- Durability is facilitated with high copper, low zinc brass castings for dezincification resistance and components made from PERMEX® rubber compound for chloramine resistance
- Adjustable tailpiece
- Valve body, Cover, Tailpiece and Control Stop shall be in compliance with ASTM Alloy Classification for Semi-Red Brass
- Valve shall be in compliance to the applicable sections of ASSE 1037

Warranty

[View Warranty Information](#)

Notes

All information contained within this document subject to change without notice.

*Compliant with ADA accessibility requirements when installed according to ADA standards.