

## piSAVE® sense 04/60 (blue), 10p, incl. Assembly tool

Article number: 0202425



- Vacuum check valves which allows a few suction cups to miss the object(s) and still maintain enough vacuum level in the system with quick response and release times.
- The vacuum check valves shall be used in a centralized vacuum system, one for each suction cup.
- Designing with vacuum check valves will require a smaller vacuum pump and save energy.
- Also suitable for objects with surface leakage around the lip of the suction cup.
- Available in four sizes with different flow performance/characteristics to suit different degree of leakage on handled material and different size of cups.
- The valves are supplied separately for integration or mounted in an AI-fitting with female and male threaded connections to facilitate installation.

### Technical data

Description	Unit	Value
Material	-	HNBR, Thermoplastic Polyurethane (TPE-U)
Temperature, max.	°C	80
Temperature, min.	°C	-20
Weight, min.	g	0.3
Pump flow/cup minimum	NI/s	0.15
Pump flow/cup to close valve	NI/s	0.55
Valve colour	-	Blue

### Material

Name	Thermoplastic Polyurethane (TPE-U)	HNBR 50° Shore A
Colour	White transparent	Blue
Temperature, min.   °C	-20	-30
Temperature max.   °C	80	140
Hardness   °Shore A	81	50

### Material resistance

Alcohol	Good	Good
Concentrated acids	Poor	Fair
Ethanol	n/a	n/a
Hydrolysis	Poor	Good
Methanol	n/a	n/a
Oil	Excellent	Excellent
Oxidation	Good	Excellent
Petrol	Poor	Excellent
Wear resistance	Excellent	Excellent
Weather and ozone	Excellent	Excellent

**Spare parts**

0202589 | piSAVE® sense Assembly tool 16mm