

Glycerine Gauges



All Stainless Steel Gauges, 1/2” Centre Back Connection

Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
2038-8435	Gly-filled	100mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/2"	0-12 bar /psi	Ambient 0-60°C	1.60%
2038-8443	Gly-filled	100mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/2"	0-20 bar / psi	Ambient 0-60°C	1.60%
2038-8450	Gly-filled	100mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/2"	0-40 bar /psi	Ambient 0-60°C	1.60%
2038-8476	Gly-filled	100mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/2"	0-250 bar /psi	Ambient 0-60°C	1.60%

