

Glycerine Gauges



Stainless Steel Case, Heavy Duty, Bottom Connection

Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
HG100-002B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-2.5 bar / psi	Ambient 0-60°C	1.00%
HG100-004B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-4 bar / psi	Ambient 0-60°C	1.00%
HG100-006B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-6 bar / psi	Ambient 0-60°C	1.00%
HG100-010B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-10 bar / psi	Ambient 0-60°C	1.00%
HG100-016B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-16 bar / psi	Ambient 0-60°C	1.00%
HG100-040B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-40 bar / psi	Ambient 0-60°C	1.00%
HG100-100B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-100 bar / psi	Ambient 0-60°C	1.00%
HG100-160B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-160 bar / psi	Ambient 0-60°C	1.00%
HG100-250B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-250 bar / psi	Ambient 0-60°C	1.00%
HG100-400B	Gly-filled	100MM	Satin s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/2"	0-400 bar / psi	Ambient 0-60°C	1.00%

