



Dry Gauges

ABS Case, Centre Back Connection



Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
G40-01R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-1 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-02R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-2 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-04R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-4 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-06R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-6 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-07R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-7 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-10R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-10 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-12R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-12 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G40-20R	Dry	40MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-20 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-01R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-1 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-02R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-2 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-04R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-4 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-06R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-6 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-10R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-10 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-12R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-12 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-20R	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/8"	0-20 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-02T	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/4"	0-2 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-04T	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/4"	0-4 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-06T	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/4"	0-6 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-10T	Dry	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/4"	0-10 BAR / PSI	AMBIENT -20 + 60°C	2.50%
G50-20T	DRY	50MM	Plastic ABS	Acrylic	Brass	Phosphor Bronze	Brass	CBM BSPT 1/4"	0-20 BAR / PSI	AMBIENT -20 + 60°C	2.50%