

Glycerine Gauges



All Stainless Steel Gauges, 1/4” Centre Back Connection

Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
2038-8583	Gly-filled	40mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-12 BAR / PSI	Ambient 0-60°C	2.50%
2038-8591	Gly-filled	40mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-20 BAR / PSI	Ambient 0-60°C	2.50%
2038-8609	Gly-filled	40mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-40 BAR / PSI	Ambient 0-60°C	2.50%
2038-8625	Gly-filled	40mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-60 BAR / PSI	Ambient 0-60°C	2.50%
2038-8633	Gly-filled	40mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-250 BAR / PSI	Ambient 0-60°C	2.50%
2038-8534	Gly-filled	63mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-12 BAR / PSI	Ambient 0-60°C	2.50%
2038-8567	Gly-filled	63mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-60 BAR / PSI	Ambient 0-60°C	2.50%
2038-8575	Gly-filled	63mm	Polished s/s 304	Polycarbonate	s/s 304	s/s 316	s/s 304	CBM BSPP 1/4"	0-250 BAR / PSI	Ambient 0-60°C	2.50%

