



Glycerine Gauges

Stainless Steel Case, Bottom Connection

Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
G63-001BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-1 bar / psi	-5°C to +60°C	2.50%
G63-002BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-2 bar / psi	-5°C to +60°C	2.50%
G63-004BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-4 bar / psi	-5°C to +60°C	2.50%
G63-006BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-6 bar / psi	-5°C to +60°C	2.50%
G63-012BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-12 bar / psi	-5°C to +60°C	2.50%
G63-020BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-20 bar / psi	-5°C to +60°C	2.50%
G63-025BPPG	Gly-filled	63mm	Polished s/s 305	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-25 bar / psi	-5°C to +60°C	2.50%
G63-040BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-40 bar / psi	-5°C to +60°C	2.50%
G63-060BPPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-60 bar / psi	-5°C to +60°C	2.50%
G63-120BPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-120 bar / psi	-5°C to +60°C	2.50%
G63-200BPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-200 bar / psi	-5°C to +60°C	2.50%
G63-400BPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-400 bar / psi	-5°C to +60°C	2.50%
G63-600BPG	Gly-filled	63mm	Polished s/s 304	Polycarbonate	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-600 bar / psi	-5°C to +60°C	2.50%

